

INTENDED USE

The CH100-3Q is a versatile, strong and stable equipment channel suitable to support lighting and equipment. It can be used as an instrument stand when space is limited.

NOTE - CH100-3Q is designed specifically as an equipment support. It is not designed with the intention of being a typical support channel.

INSTRUCTION FOR USE

Install the Mekano® starter bracket to the structure in the desired location.
Fit the equipment channel to the starter bracket using M10 self-locking bolts and anti-vibration nuts. Adjust and tighten with recommended torque. Fasten additional brackets and equipment as needed.

Fasten brackets, channels or equipment using standard M10x20 self-locking bolts and anti-vibration flange nuts.

When pulling cables through the access holes, use the Edge Protector to protect the cable from sharp edges.





User Guide for Bolts:
Recommended Torque

Can be used as instrument stand when space is limited



Compatible with accessories with M10 bolts



Back-to-back channel connection using M10x25 self-locking bolts and anti vibration flange nuts

