USER GUIDE · INKO® MODULE TUBING CLAMP SS



INTENDED USE


INKO® module tubing clamp is designed for fast assembly to fit Oglaend cable tray lateral slots (Adapter brackets are available for longitudinal slots), Mekano® Channels, Hilti M10 channels and FoS. All clamp bodies are available with bases for bolting with M6, M10 and FoS (M12).

INSTRUCTION FOR USE


Tubing Clamps

- Install Bolted base unit to a mounting surface by supplied fasteners. Make sure there is no collision between bolt/stud and Tube.
- Position the Lower clamp half into the module base.
 1. For non-grip installation place the adapter onto lower clamp half.
- 3. Install tubing line.
- 4. Add the Top tube clamp half.
- 5. Fix the lock pate with the max torque of 3Nm.

EXAMPLE OF CONNECTIONS




STACKING PRINCIPLE



NON-GRIP INSTALLATION

Free tube axial expansion



FIXED INSTALLATION

